



FOCAL LENGTH (EFL): 30 ±0,3
 BACK FOCAL LENGTH (BFL): 28,77

- 1 AR COATING: UV-AR
 - R(ABS) ≤ 1,0% FROM 250-425nm @ 0° AOI
 - R(AVG) ≤ 0,75% FROM 250-425nm @ 0° AOI
 - R(AVG) ≤ 0,5% FROM 370-420nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	26,943±0,027 CX	GLASS FUSED SILICA 458/678	R	26,943±0,027 CX
Øe	11		Øe	11
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	2,18'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED		FIRST ANGLE PROJECTION		
ROHS: COMPLIANT	SCALE: NONE λ = 587,6nm			
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			TITLE	12mm Dia, x 30mm FL, UV-AR Coated, UV Double-Convex Lens
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING			ALL DIMS IN: mm	DWG NO
INDICATIONS IN ACCORDANCE WITH ISO 10110			SHEET SIZE	A4
				SHEET 1 OF 1