



FOCAL LENGTH (EFL): 60 ±0,6
 BACK FOCAL LENGTH (BFL): 58,67

- 1 AR COATING: YAG-BBAR
 - R(ABS) < 0,25% @ 532nm @ 0° AOI
 - R(ABS) < 0,25% @ 1064nm @ 0° AOI
 - R(AVG) < 1,0% FROM 500-1100nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	61,33±0,061 CX	GLASS N-BK7 517/642	R	61,33±0,061 CX
Øe	19		Øe	19
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED		FIRST ANGLE PROJECTION			
ROHS: COMPLIANT	SCALE: NONE λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			TITLE	20mm Dia, x 60mm FL, YAG-BBAR Coated, Double-Convex Lens	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING			ALL DIMS IN:	DWG NO	89262
INDICATIONS IN ACCORDANCE WITH ISO 10110		mm			SHEET 1 OF 1