

TECHSPEC® DRACONIS™ Nd:YAG LASER LINE BEAM EXPANDERS

1064nm • 10X #59-130

- Designed for Nd:YAG Wavelengths 532nm and 1064nm
- $\lambda/10$ Transmitted Wavefront
- Collimation Adjustment Using Non-Rotating Optics Minimizes Beam Wander
- TECHSPEC® Draconis™ Broadband Beam Expanders Also Available



TECHSPEC® Draconis™ Nd:YAG Laser Line Beam Expanders feature high performance optical designs that have been optimized and tested for YAG laser wavelengths. These beam expanders offer diffraction-limited performance over large input beam diameters and wide acceptance angles, eliminating the need for critical alignment. The provided focus adjustment can also be used for divergence correction or collimation. Due to the lack of ghost images focusing on internal surfaces, these beam expanders ensure compatibility with high power lasers. TECHSPEC® Draconis™ Nd:YAG Laser Line Beam Expanders C and T input/output mounting threads are compatible with Edmund Optics' line of threaded mounting components, or mounting can be achieved using an optional mounting clamp. Laser Beam Expanders are ideal for any Nd:YAG application including laser cutting, welding, or marking.

For more information on beam expanders and their application, please see online for our Technical Resource: [Application Note on Beam Expanders](#)

Wavelength Range:	1030-1100nm
Expansion Power:	10X
Entrance Aperture:	8mm
Exit Aperture:	33mm
Transmitted Wavefront, P-V:	$\lambda/10$ @ 1064nm @ 1mm Input Beam $\lambda/4$ @ 1064nm @ 3mm Input Beam
Mounting Threads:	Input: Male C-Thread (1" x 32 TPI) Output: Male T2-Thread (M42 x 0.75)
Substrate:	Fused Silica
Housing Diameter:	46mm
Length:	98mm
Angle of Incidence:	0°
Coating:	Laser V-Coat (1064nm)
Coating Specification:	$R_{\text{abs}} < 0.25\%$ @ 1063 - 1065nm $R_{\text{avg}} < 0.5\%$ @ 1030 - 1100nm
Divergence Adjustment:	Non-Rotating Optics

