


Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

750nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

750nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

800nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

800nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

850nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

850nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

900nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

900nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

950nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

950nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

1000nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

COATING CURVE


1000nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

1050nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

1050nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

1100nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

COATING CURVE


1100nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

725nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

725nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

775nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

COATING CURVE


775nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

825nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

825nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

875nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

875nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

925nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

925nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

975nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

975nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

1025nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

COATING CURVE


1025nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

1075nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

1075nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



COATING CURVE