


# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 750nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 750nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 800nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 800nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 850nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 850nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 900nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 900nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE



# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 950nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 950nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 1000nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 1000nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 1050nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 1050nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 1100nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE

## 1100nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY






# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 400nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 400nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 425nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 425nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE


## 450nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 450nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 475nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 475nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



COATING CURVE




# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE


## 500nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 500nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 525nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 525nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 550nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 550nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 575nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 575nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE



# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 600nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 600nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 625nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 625nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 650nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 650nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 675nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 675nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE



# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 700nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE

### 700nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE


## 725nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 725nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 775nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE


**775nm Techspec® Shortpass Filter: OD >4.0 Coating Performance  
FOR REFERENCE ONLY**



# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 825nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 825nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE



# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 875nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 875nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 925nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 925nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 975nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 975nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 1025nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE

## 1025nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY






# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 1075nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 1075nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



COATING CURVE