


# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE

## 750nm High Performance Longpass Filter, OD >4.0 Coating Performance FOR REFERENCE ONLY




# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE

## 750nm High Performance Longpass Filter OD >4.0 Coating Performance FOR REFERENCE ONLY




# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE

## 800nm High Performance Longpass Filter, OD >4.0 Coating Performance FOR REFERENCE ONLY




# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE

## 800nm High Performance Longpass Filter OD >4.0 Coating Performance FOR REFERENCE ONLY




# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE

## 850nm High Performance Longpass Filter, OD >4.0 Coating Performance FOR REFERENCE ONLY




# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE

## 850nm High Performance Longpass Filter OD >4.0 Coating Performance FOR REFERENCE ONLY




# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE

## 900nm High Performance Longpass Filter, OD >4.0 Coating Performance FOR REFERENCE ONLY




# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE

## 900nm High Performance Longpass Filter OD >4.0 Coating Performance FOR REFERENCE ONLY






# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE

## 950nm High Performance Longpass Filter, OD >4.0 Coating Performance FOR REFERENCE ONLY




# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE

## 950nm High Performance Longpass Filter OD >4.0 Coating Performance FOR REFERENCE ONLY




# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE

## 1000nm High Performance Longpass Filter, OD >4.0 Coating Performance FOR REFERENCE ONLY




# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE

## 1000nm High Performance Longpass Filter OD >4.0 Coating Performance FOR REFERENCE ONLY




# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE


## 1050nm High Performance Longpass Filter, OD >4.0 Coating Performance FOR REFERENCE ONLY



# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 1050nm High Performance Longpass Filter OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE

## 1100nm High Performance Longpass Filter, OD >4.0 Coating Performance FOR REFERENCE ONLY




# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE

## 1100nm High Performance Longpass Filter OD >4.0 Coating Performance FOR REFERENCE ONLY






# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE

## 725nm High Performance Longpass Filter, OD >4.0 Coating Performance FOR REFERENCE ONLY




# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE

## 725nm High Performance Longpass Filter OD >4.0 Coating Performance FOR REFERENCE ONLY




# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE

## 775nm High Performance Longpass Filter, OD >4.0 Coating Performance FOR REFERENCE ONLY




# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE

## 775nm High Performance Longpass Filter OD >4.0 Coating Performance FOR REFERENCE ONLY




# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE


## 825nm High Performance Longpass Filter, OD >4.0 Coating Performance FOR REFERENCE ONLY



# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 825nm High Performance Longpass Filter OD >4.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE


## 875nm High Performance Longpass Filter, OD >4.0 Coating Performance FOR REFERENCE ONLY



# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

## 875nm High Performance Longpass Filter OD >4.0 Coating Performance FOR REFERENCE ONLY



COATING CURVE




# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE

## 925nm High Performance Longpass Filter, OD >4.0 Coating Performance FOR REFERENCE ONLY




# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE

## 925nm High Performance Longpass Filter OD >4.0 Coating Performance FOR REFERENCE ONLY




# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE

## 975nm High Performance Longpass Filter, OD >4.0 Coating Performance FOR REFERENCE ONLY




# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE

## 975nm High Performance Longpass Filter OD >4.0 Coating Performance FOR REFERENCE ONLY




# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE

## 1025nm High Performance Longpass Filter, OD >4.0 Coating Performance FOR REFERENCE ONLY




# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE

## 1025nm High Performance Longpass Filter OD >4.0 Coating Performance FOR REFERENCE ONLY




# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE

## 1075nm High Performance Longpass Filter, OD >4.0 Coating Performance FOR REFERENCE ONLY



# Coating Curve

Edmund Optics Inc.  
USA | Asia | Europe

COATING CURVE

## 1075nm High Performance Longpass Filter OD >4.0 Coating Performance FOR REFERENCE ONLY

