

1200 GROOVES, 12.7 X 12.7MM UV HOLOGRAPHIC GRATING

250 - 400nm • #43-772


- Groove Density up to 3600 Grooves per mm
- Bare Aluminum Coating
- Sinusoidal Grating Profile



Groove Density (grooves/mm):	1200
Blaze Wavelength (nm):	250 - 400
Dimensions (mm):	12.7 x 12.7
Dimensional Tolerance (mm):	±0.5
Coating:	Bare Aluminum
Construction:	Holographic Grating

Substrate:	Float Glass
Thickness (mm):	6.00
Thickness Tolerance (mm):	±0.5
Type:	Reflective Diffraction Grating
Absolute Diffraction Efficiency (%):	45 - 65
Alignment of Grooves to Edge (°):	±0.5

1200 Grooves/mm, UV Holographic Grating Absolute Efficiency



© COPYRIGHT 2020 EDMUND OPTICS, INC. ALL RIGHTS RESERVED