




NOTES:

1. COATING:
S1: MAXIBLACK™
THICKNESS: 4 - 6 (µm)
2. ABSORBANCE: 98%
3. ABRASION RESISTANCE: MODERATE
4. HUMIDITY RESISTANCE: MIL-C-48497A
5. OPERATING TEMPERATURE (°C): -250 TO +290
6. WAVELENGTH RANGE (µm): 0.3 - 5




DETAIL A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO® Edmund Optics®

THIRD ANGLE PROJECTION 		TITLE	20 x 20cm Sheet of MaxiBlack Film, No Adhesive	
ALL DIMS IN	mm	DWG NO	20049	SHEET 1 OF 1