


NOTES:


1. SUBSTRATE: POLYMER FILM XP42 ON 0.5 mm PMMA
2. OPERATING TEMPERATURE: -40 TO +80
3. WAVELENGTH RANGE: 400-700nm
4. POLARIZATION: >99.98
5. TRANSMISSION (%):
 SINGLE 42 ±2
 PARALLEL: 36.4
 CROSSED: <0.004
6. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

THIRD ANGLE PROJECTION 		TITLE	600 x 900mm Linear Polarizer (XP42-70)	
ALL DIMS IN	mm	DWG NO	19950	SHEET 1 OF 1